

Technical data sheet 570B

Specification Cantilever frame with armrests, mesh backrest

Dimensions in mm

Seat:	H:	470
	W:	450
	D:	410
Total:	H:	930
	W (ArmR):	610
	D:	540

Packaging data	Weight:	kg	8
	Volume:	m³	0,4



Basic equipment

Benefit

Backrest	Meshback, black.	

Upholstery	Seat upholstery: 55 mm foam.	Great seating comfort.

Frame	Tubular steel frame Ø 22 x 2,5 mm, powder coated as colour finish (plastic parts).	

Seat carrier.	Plastic.	

Stackability.	4 chairs.	Diverse use of space.

Plastic parts	Colour maintained throughout, black.	Colourfast and resistant to deep scratches and abrasions.

Armrests	Plastic, colour maintained throughout, black.	The armrests relieve the neck and shoulder muscles.

Materials	All materials are segregated and recyclable.	Environmentally friendly.

Standards	EN 16139 for visitor chairs. GS-Symbol for tested safety and tested for contaminants.	High-quality and great comfort.

Certification	Quality management system DIN EN ISO 9001:2008, VO (EG) No. 1221/2009 (EMAS), Environmental management system DIN EN ISO 14001:2009, OHSAS, EcoVadis gold, Commitment to sustainability. Blue Angel, Bifma e3 level Platin.	High-quality product.

Warranty and return	10 years warranty. Complete return and recycling guarantee.	Exchange of parts free of charge within the guaranteed periods.

Disassembly instructions are available upon request for any interstuhl product

Technical data sheet 570B

Specification Cantilever frame with armrests, mesh backrest

Dimensions in mm

Seat:	H:	470
	W:	450
	D:	410
Total:	H:	930
	W (ArmR):	610
	D:	540

Packaging data	Weight:	kg	8
	Volume:	m³	0,4



Options		Benefit
Backrest	Meshback, white, flame red, traffic orange, may green, beige grey, iron grey, cobalt blue, pastel blue.	
Plastic parts and frame	White.	Optical design.
Frame	Powder coated brilliant-silver or chromed.	Optical design.
Glides	Felt glides for hard floors.	Ideal stability and protection of the floor.
Materials (fabric)	Several fabric collections and leather in various colours.	Individual design.

Disassembly instructions are available upon request for any interstuhl product